





## Download DXF 2D 858 dyf Montaggi - Minicomfort.pdf



596/1196

## 859 Minicomfort T5 high-gloss 99.85

Housing: galvanized steel stove pre-enamelling. Louvre: Dark light Dark light double parabolic louvres, in high-gloss plated aluminium 99.85. Anti-dazzle and anti-iridescence, very low luminance. PVD treatment.

Lampholder: In polycarbonate, with contacts in phosphor bronze.

Electric gear: Automatic line and are 100% tested on the line 230V/50Hz electronic power supply. Hard wire, 0.50 sqmm cross section, and PVC-HT sheath, resistant up to 90°C, according to CEI 20-20 standards. 2P+T terminal block, with maximum allowed lead cross section of 2.5 sqmm.

Equipment: Quick connectors for electrical line and with door for electrical connections.

Snap fastening optics, which remain attached with nylon cords.

Anti-fingerprint gloves to avoid damage to the louvre during installation. Mounting: Recessed for contact mounting on the cross T structure Regulations:Produced according to applicable EN60598 CEI 34-21 standards, IP20IK07 degree of protection according to EN 60529. These products can be installed on normally inflammable surfaces. Emergency light version: In maintened version. In the event of a block surface

Emergency light version: In maintained version. In the event of a black-out a single lamp connected to the back-up circuit continues to operate. Run time 60 minutes. On request: optional "Main Control System" available for emergency management.

Minimum size of hole for recessed installation: Mini Comfort 4x14/3x14/2x14(600x600) = 572x572mm

Mini Comfort 2x14 = 572x270mm

Mini Comfort 4x28/3x28 = 1172x572mm

Mini Comfort 2x28 = 1172x270mm

Gear	Kg	Lumen-K-CRI	WTot	Base	Colour
CELL-E	2.85	FL 4x14-1250lm-4000K-Ra 1b	69 W	G5	WHITE
CELL-DH	7.80	FL 4x28-2650lm-4000K-Ra 1b	128 W	G5	WHITE
CELL	3.00	FL 4x14-1250lm-4000K-Ra 1b	66 W	G5	WHITE
CELL-D-D	2.91	FL 4x14-1250lm-4000K-Ra 1b	62 W	G5	WHITE
CELL-DH	3.00	FL 4x14-1250lm-4000K-Ra 1b	62 W	G5	WHITE
CELL-E	6.50	FL 4x28-2650lm-4000K-Ra 1b	132 W	G5	WHITE
CELL	5.80	FL 4x28-2650lm-4000K-Ra 1b	128 W	G5	WHITE
CELL-D-D	7.80	FL 4x28-2650lm-4000K-Ra 1b	124 W	G5	WHITE
	CELL-E CELL-DH CELL CELL-D-D CELL-DH CELL-E CELL	CELL-E 2.85   CELL-DH 7.80   CELL 3.00   CELL-D-D 2.91   CELL-DH 3.00   CELL-E 6.50   CELL 5.80	CELL-E 2.85 FL 4x14-1250lm-4000K-Ra 1b   CELL-DH 7.80 FL 4x28-2650lm-4000K-Ra 1b   CELL 3.00 FL 4x14-1250lm-4000K-Ra 1b   CELL-D-D 2.91 FL 4x14-1250lm-4000K-Ra 1b   CELL-DH 3.00 FL 4x14-1250lm-4000K-Ra 1b   CELL-DH 3.00 FL 4x14-1250lm-4000K-Ra 1b   CELL-DH 3.00 FL 4x14-1250lm-4000K-Ra 1b   CELL-E 6.50 FL 4x28-2650lm-4000K-Ra 1b   CELL 5.80 FL 4x28-2650lm-4000K-Ra 1b	CELL-E 2.85 FL 4x14-1250lm-4000K-Ra 1b 69 W   CELL-DH 7.80 FL 4x28-2650lm-4000K-Ra 1b 128 W   CELL <dh< td=""> 3.00 FL 4x14-1250lm-4000K-Ra 1b 66 W   CELL-DD 2.91 FL 4x14-1250lm-4000K-Ra 1b 62 W   CELL-DH 3.00 FL 4x14-1250lm-4000K-Ra 1b 62 W   CELL-DH 3.00 FL 4x14-1250lm-4000K-Ra 1b 62 W   CELL-DH 3.00 FL 4x14-1250lm-4000K-Ra 1b 62 W   CELL-E 6.50 FL 4x28-2650lm-4000K-Ra 1b 132 W   CELL 5.80 FL 4x28-2650lm-4000K-Ra 1b 128 W</dh<>	CELL-E 2.85 FL 4x14-1250Im-4000K-Ra 1b 69 W G5   CELL-DH 7.80 FL 4x28-2650Im-4000K-Ra 1b 128 W G5   CELL 3.00 FL 4x14-1250Im-4000K-Ra 1b 66 W G5   CELL 3.00 FL 4x14-1250Im-4000K-Ra 1b 66 W G5   CELL-DD 2.91 FL 4x14-1250Im-4000K-Ra 1b 62 W G5   CELL-DH 3.00 FL 4x14-1250Im-4000K-Ra 1b 62 W G5   CELL-DH 3.00 FL 4x14-1250Im-4000K-Ra 1b 62 W G5   CELL-DH 3.00 FL 4x28-2650Im-4000K-Ra 1b 62 W G5   CELL-E 6.50 FL 4x28-2650Im-4000K-Ra 1b 132 W G5   CELL-E 5.80 FL 4x28-2650Im-4000K-Ra 1b 128 W G5

The reported luminous flux is the flux emitted by the light source with a tolerance of ± 10% compared to the indicated value. The W tot column indicates the total wattage absorbed by the system without exceeding 10% of the indicated